



Graver Technologies

FILTRATION | SEPARATION | PURIFICATION



Product Specifications

Media/Support/Cage: Polypropylene

End Caps: Polypropylene

Gaskets/O-Rings:

Buna-N, EPDM, Silicone, Viton

Micron rating:

1, 3, 5, 10, 20, 40, 60, 75, 100 μ m

Dimensions

Nominal lengths:

20" 40" 60"

50.8 101.6 152.4 cm

Outside diameter: 6.0" (15.2 cm)

Surface Area:

24 ft² (2.2 m²) per 20" element

49 ft² (4.6 m²) per 40" element

73 ft² (6.8 m²) per 60" element

Operating Parameters

Maximum operating

temperature: 176°F (80°C)

Maximum differential pressure:

75 psid @ 70°F (5.2 bar @ 21°C)

30 psid @ 176°F (2.0 bar @ 80°C)

Maximum reverse pressure:

40 psid @ 70°F (2.8 bar @ 21°C)

Recommended change-out pressure:

35 psid (2.4 bar)

Maximum flow rates*:

60" element up to 500 GPM (1892 lpm)

40" element up to 350 GPM (1325 lpm)

20" element up to 175 GPM (662 lpm)

*Consult factory for sizing assistance
based on particle loads.

High Flow Series Filter Cartridges

Large Geometry Pleated Filters for High Flow

Graver High Flow Series filters feature a larger geometry to handle higher flows with fewer filter elements. The result is much faster, easier filter changeouts. In addition, the inside to outside flow allows for excellent dirt holding capacity, extending the time between filter changeouts. Filter housings are also available and because of the filter's high flow and dirt holding capacity, smaller systems are possible, reducing upfront capital costs.

FEATURES & BENEFITS

- 6" diameter, large geometry for high flow rates
- Absolute retention ratings from 1 to 100 microns
- Capable of flow rates up to 500 GPM in a single 60" element
- Inside-out flow retains contaminant even during changeout
- Multi layer pleated construction with optimized surface area
- Unique Quad Seal gasket provides maximum seal integrity
- Retrofits competitive high flow filter housings
- Thermally bonded construction
- Hard Cage Option to prevent media possible extrusion problem

CERTIFICATIONS


- FDA Listed Materials: All materials comply with FDA Title 21 of the Code of Federal Regulations Sections 174.5, and 177.1520, 177.2600 as applicable for food and beverage contact.
- European Directive for Direct Food Contact: European Regulation No. 1935/2004 and European Regulation 10/2011 with amendments and corrections from European Reg N. 2020/1245: Tested for migration behavior and is suitable for contact with all kinds of foodstuffs with minimal rinse-up. Data available upon request.
- NSF 61: Certified to NSF/ANSI STD 61 for materials requirements only — Component.

TYPICAL APPLICATIONS

- Water Systems
- Chemicals
- Food and Beverage
- Pre RO



Standard – Netting



Option – Hard Cage

HIGH FLOW SERIES NOMENCLATURE INFORMATION

Product Series	Retention Rating (microns)		Length (inches)	Gasket or O-Ring	Option	Packaging
HF Series	1	20	-20	B Buna-N	-HC Hard Cage	Blank Individual Box
	3	40	-40	E EPDM		2 pk 2 Pack Box, 60" Only, w/out hard cage
	5	60	-60	S Silicone		4 pk 4 Pack Box, 60" Only, w/out hard cage
	10	75		V Viton		
		100				
Example: HF 5-60E-HC						
HF	5		-60	E	-HC	

HIGH FLOW PRESSURE DROP

Micron	Element Pressure Drop psid/gpm			Element Pressure Drop Mbar/M3/Hr		
	20"	40"	60"	20"	40"	60"
1	0.0200	0.0097	0.0065	6.0845	2.9395	1.9820
3	0.0167	0.0081	0.0054	5.0705	2.4495	1.6516
5	0.0076	0.0037	0.0025	2.3179	1.1198	0.7550
10	0.0046	0.0022	0.0015	1.3908	0.6719	0.4530
20	0.0021	0.0010	0.0007	0.6374	0.3079	0.2076
40	0.0017	0.0008	0.0006	0.5215	0.2520	0.1699
60	0.0015	0.0007	0.0005	0.4552	0.2199	0.1483
75	0.0012	0.0006	0.0004	0.3636	0.1815	0.1204
100	0.0010	0.0005	0.0003	0.3035	0.1466	0.0989

For chemical compatibility, flow rates, and temperature requirements please consult the factory or your local Graver distributor.

REMOVAL EFFICIENCY

Beta Ratio Efficiency	Beta 1000 99.9%	Beta 100 99%	Beta 10 90%
1 µm	1.0	0.6	0.2
3 µm	3.0	2.0	1.5
5 µm	5.0	4.0	3.0
10 µm	10.0	8.5	6.5
20 µm	22.0	19.0	14.0
40 µm	38.0	18.0	15.0
60 µm	60.0	35.0	20.0
75 µm	75.0	48.0	35.0
100 µm	100.0	75.0	45.0

$$\text{Beta Ratio} = \frac{\text{Upstream particle counts}}{\text{Downstream particle counts}}$$

The micron ratings shown at various efficiency and beta ratio value levels were determined through laboratory testing, and can be used as a guide for selecting cartridges and estimating their performance. Under actual field conditions, results may vary somewhat from the values shown due to the variability of filtration parameters.

Testing was conducted using the single-pass test method, water at 3 gpm/10" cartridge. Contaminants included latex beads, coarse and fine test dust. Removal efficiencies were determined using dual laser source particle counters.



Certified to
NSF/ANSI/CAN 61

FOR MORE INFORMATION

Customer Service/Technical Support: 1-888-353-0303 info@gravertech.com

China: +86-21-5238-6576 Asia: +65-9671-9966

All information and recommendations appearing in this bulletin concerning the use of products described herein are based on tests believe to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Graver Technologies as to the effects of such use or the results to be obtained. Graver Technologies assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations. TPE is a trademark of Graver Technologies, LLC.



Graver Technologies | 302-731-1700 | 800-249-1990
info@gravertech.com | www.gravertech.com

A member of The Marmon Group—A Berkshire Hathaway Company

GTX-322 8-25

DISTRIBUTED BY