



Graver Technologies

FILTRATION | SEPARATION | PURIFICATION



MBC™ Series Filter Cartridges

Melt Blown Filters

Product Specifications

Media: Polypropylene

End caps/Center Core: Polypropylene

Gaskets/O-Rings:

Buna-N, EPDM, Santoprene,
Silicone, Teflon Encapsulated
Viton (O-Rings only), Viton

Micron rating:

1, 3, 5, 10, 20, 30, 50, 75 µm

Dimensions

Nominal lengths:

5", 9.75", 10", 19.5", 20", 29.25", 30",
39", 40"

(12.7, 24.8, 25.4, 49.5, 50.8, 74.3, 76.2,
99.1, 101.6 cm)

(Other lengths available)

Outside diameter: 2.5" (6.35 cm),
2.63" (6.7 cm) End capped

Inside diameter: 1.0" (2.54 cm)

Operating Parameters

Maximum differential pressure:


150 psid @ 68°F (10.3 bar @ 20°C)

90 psid @ 150°F (6.2 bar @ 66°C)


35 psid @ 176°F (2.4 bar @ 80°C)

Recommended change-out pressure:


35 psid (2.4 bar)




Outer
prefilter
zone



Inner
prefilter
zone



Final
pre-filter
zone



Final
filtration
zone

An economical, melt blown filter element that can be used in a wide range of applications. The MBC depth filter is constructed of 100% polypropylene media for chemical compatibility with a variety of process fluids. The molded core prevents collapse even at elevated temperatures.

FEATURES & BENEFITS

- Available in nominal ratings from 1 to 75 microns
- Molded core for excellent collapse strength
- Graded pore construction for long on-stream life
- Melt blown media resists dirt unloading as differential pressure increases
- Non-shedding
- High dirt holding capacity
- Economical depth filtration
- Thermal bonded endcaps optional
- Free of binders, adhesives and surfactants

CERTIFICATIONS

- USP Class VI: Meets USP Class VI Biological Test for Plastics
- FDA Listed Materials: All materials comply with FDA Title 21 of the Code of Federal Regulations Sections 174.5, 177.1520 and 177.2600, as applicable for food and beverage contact.
- NSF 61: Certified to NSF/ANSI STD 61 for materials requirements only — Component
- European Directive for Direct Food Contact: European Regulation No. 1935/2004 and European Regulation 10/2011: Tested for migration behavior and is suitable for contact with all kinds of foodstuffs with minimal rinse-up. Data available upon request.
- Paint Wetting Impairment Substances (PWIS)/Lackbenetzungsstörende Substanzen (LABS): Filter media tested to VDMA 24364:2018-05 standards to ensure optimal paint adhesion.

TYPICAL APPLICATIONS

- RO Prefilters
- Wastewater
- Chemicals
- Blowdown post filter
- Radwaste
- Aqueous solutions
- Inks


MBC NOMENCLATURE INFORMATION

Filter Type	Retention Rating (microns)		Nominal Length (inches)		End Configuration		Gasket or O-Ring	
MBC Series	1	20	-5	-29.25	P	Double Open End (Hard Endcaps)	B	Buna-N
	3	30	-9.75	-30	P2	226/Flat Single Open End	E	EPDM
	5	50	-10	-39	P3	222/Flat Single Open End	N	None
	10	75	-19.5	-40	P5	222/Spring Single Open End	S	Silicone
			-20		P6	Self-Seal Spring on One End	T	Teflon encap.
					P7	226/Fin Single Open End	Viton	(O-Rings only)
					P8	222/Fin Single Open End	V	Viton
					P15	DBG/Spring Single Open End		
					P28	222 w/3 tabs/Fin Single Open End		
					PX	Extended Core (Cut Ends)		
Example: MBC 10-20NN					PX*	Flat Gasket/Flat Gasket w/Extended Core ¹		
					N	None (Cut Ends)		
					DBG	Direct Bond Santoprene Gaskets		
					AM	Single Open End, Internal O-Ring		
MBC	10		-20		N		N	

¹Need a gasket material for the *

MBC FLOW RATE

Typical Flow Rate Clean Water at Ambient Temperature
(per 10" cartridge)



For liquids other than water, multiply pressure drop by the fluid viscosity in centipoise



Certified to
NSF/ANSI/CAN 61

FOR MORE INFORMATION

GTX-329 9-25

DISTRIBUTED BY

Customer Service/Technical Support: 1-888-353-0303

China: +86-21-5238-6576 Asia: +65-9671-9966

All information and recommendations appearing in this bulletin concerning the use of products described herein are based on tests believe to be reliable. However, It is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Graver Technologies as to the effects of such use or the results to be obtained. Graver Technologies assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations. TPE is a trademark of Graver Technologies, LLC.



Graver Technologies | 200 Lake Drive, Glasgow, DE 19702 | 1-302-731-1700 | 800-249-1990
Fax: 1-302-369-0938 | info@gravertech.com | www.gravertech.com

A member of The Marmon Group—A Berkshire Hathaway Company