

IRt/c tested for vacuum and microwave compatibility

Tests for compatibility performed by customers contribute greatly to our understanding of how IRT/cs perform in some of the unusual environments where non-contact temperature measurements are required. CleverIR has a policy of providing sample sensors with R&D discount for test purposes, in return for a copy of test results. This series of tests was performed by a customer who required the performance, and had the facility to test the IRT/c. The test was conducted in a 1.2 m by 1,2 m (4 ft. by 4 ft.) chamber in the following sequence:

First Test

1. Vacuum exposure (15 minutes at 40 Torr)
2. Microwave Exposure (5 minutes, 3 KW at 2450 MHz)
3. Chamber load (6.8 kg H2O)

Second Test

1. Vacuum exposure (10 minutes)
2. Microwave Exposure (30 seconds, 3 KW at 2450 MHz)
3. Microwave Exposure (10 seconds, 3 KW at 2450 MHz)
4. Chamber load (0.47kg H2O)

The IRT/c showed no ill effects and operated flawlessly when checked after the test sequence.