


INPUT PANELS



PLI-434
5 Cam-Lok
24 circuits per leg, 3-RU

PLI-435
5 Cam-Lok, 24 circuits per leg
rev gnd, 3-RU

PLI-436
5 Cam-Lok, 24 circuits per leg
rev gnd, rev neu, 3-RU


PLI-440
10 Cam-Lok
24 circuits per leg, 4-RU

PLI-441
10 Cam-Lok
24 circuits per leg
rev gnd, 4-RU

PLI-442
10 Cam-Lok, 24 circuits per leg
rev gnd, rev neu, 4-RU

PLI-446
6 Cam-Lok
24 circuits per leg, 3-RU

INPUT PANELS



PLI-447
6 Cam-Lok, 24 circuits per leg
rev gnd, 3-RU

PLI-448
6 Cam-Lok, 24 circuits per leg
rev gnd, rev neu, 3-RU

PLI-452
12 Cam-Lok
24 circuits per leg, 4-RU

PLI-453
12 Cam-Lok
24 circuits per leg
rev gnd, 4-RU

PLI-454
12 Cam-Lok
24 circuits per leg
rev gnd, rev neu, 4-RU