

All-Metal Separator

Electronic detection and removal of metal residues using a flap mechanism. Combining the separator with the MAG 14.000 allows upstream separation of ferrous particles and reduces the loss of usable material.

All-metal separator



- + Mobile all-metal separator
- + Combinable with the MAG 14.000
- + High efficiency in the removal of metallic residues

Article No.	L [mm]	B [mm]	H [mm]	Conn. Ø	Weight [kg]
MMA-0380	450	450	300	38	approx. 35.0
MMA-0450	450	450	300	45	approx. 35.0
MMA-0500	450	450	300	50	approx. 35.0
MMA-0550	450	450	300	55	approx. 35.0
MMA-0600	450	450	300	60	approx. 35.0
MMA-0650	450	450	300	65	approx. 35.0
MMA-0700	450	450	300	70	approx. 35.0

Frame for All-Metal Separator

Article No.	L [mm]	B [mm]	H [mm]	Conn. Ø	Weight [kg]
MMA-GES	*	*	*	*	*

* Designed to fit the all-metal separator.

Open product page

en.michel-tube.com/allmetallabscheider

