



VALVE STEM MOUNT NOTES:

OPTI CERTIFIED HARDWARE

1. CONTACT OPTIRTC SALES AT [HTTPS://OPTIRTC.COM/CONTACT/](https://optirtc.com/contact/) OR (844) 678-4782 EXT. 3 FOR OPTI CERTIFIED HARDWARE:
 - 1.1. VALVE STEM EXTENSION (TO BE DELIVERED WITH VALVE)
 - 1.2. 12" x 1 5/8 IN. STRUT CHANNEL
 - 1.3. 18" x 1/2 IN. ANCHOR RODS (2 PER STRUT)
 - 1.4. STRUT-MOUNT ROUTING CLAMPS (2 PER STRUT)
2. ALL BRACKET MATERIALS MUST BE #304 STAINLESS STEEL.
3. MINIMUM SPACING: 1 VALVE STEM MOUNT FOR STEM LENGTH BELOW 3 FEET. ADD VALVE STEM MOUNTS PER ADDITIONAL 3 FEET OF STEM LENGTH.
4. 1/2 IN. ANCHOR ROD TO BE SET USING INJECTABLE ADHESIVE ANCHOR WITH AUTO CLEANING DRILL BIT OR CLEAN HOLE THOROUGHLY WITH COMPRESSED AIR. USE QUIKRETE HIGH STRENGTH ANCHORING EPOXY (PRODUCT #8620-31) OR EQUIVALENT. ROD SET IN CONCRETE MIN 3 IN..

1	VALVE STEM MOUNT DETAIL
2	WALL MOUNTED



OPTIRTC, INC.
 98 NORTH WASHINGTON ST.
 SUITE 210
 BOSTON, MA 02114
 (844) 678-4782

VALVE STEM MOUNT

NOT FOR CONSTRUCTION
 REFERENCE USE ONLY
 NOT TO SCALE
 © OPTIRTC, INC. 2026
 ALL RIGHTS RESERVED

REVISED: 04/14/2026

DRAWING NUMBER:
 VSM-1