





Opus One SN219 Channel Summary

Number of Channels: 2



Copyright (c) 2026 by Quantum Opus, LLC

Channel Information		Measurement		
Optical Ch	1	Operating Temperature	2.2 K	
Electrical Ch	1	Operating Current	8.7 μ A	
Wavelength	1310, 1550 nm	Dark Count Rate ¹	100 cps	
Fiber Type	SMF-28	Absolute Efficiency ²	1310 nm	92 %
Output Pulse	Digital		1548 nm	89 %
Output Voltage	1.0 V	Recovery Time ³	10 %	32 ns
Circuit	Anti-latch High Count Rate with Cryoamp	1548 nm	50 %	41 ns
			90 %	57 ns
		Timing Jitter ⁴	62 ps	



¹Dark Counts measured with the fiber port blocked with a protective cap to shield the system from stray light.

²Absolute Efficiency measured using a CW optical source at a count rate <300 kcps. For measurements in the range of 1260–1600 nm relative uncertainty is $\pm 2\%$, otherwise it is $\pm 4\%$.


³For details on recovery time measurement see: <https://quantumopus.com/dl/Oshiro2025.pdf>.

⁴FWHM. Deconvolved from autocorrelation measurement with 9 ps time-tagger measurement jitter, 8 ps 1550 nm optical pulse. Estimated ± 2 ps error.

Further details on measurements are available upon request.

For system support, maintenance, or upgrades contact support@quantumopus.com.

Channel Information		Measurement		
Optical Ch	2	Operating Temperature	2.2 K	
Electrical Ch	2	Operating Current	8.9 μ A	
Wavelength	1310, 1550 nm	Dark Count Rate ¹	100 cps	
Fiber Type	SMF-28	Absolute Efficiency ²	1310 nm	93 %
Output Pulse	Digital		1548 nm	91 %
Output Voltage	1.0 V	Recovery Time ³	10 %	32 ns
Circuit	Anti-latch High Count Rate with Cryoamp	1548 nm	50 %	40 ns
			90 %	55 ns
		Timing Jitter ⁴	62 ps	



¹Dark Counts measured with the fiber port blocked with a protective cap to shield the system from stray light.

²Absolute Efficiency measured using a CW optical source at a count rate <300 kcps. For measurements in the range of 1260–1600 nm relative uncertainty is $\pm 2\%$, otherwise it is $\pm 4\%$.

³For details on recovery time measurement see: <https://quantumopus.com/dl/Oshiro2025.pdf>.

⁴FWHM. Deconvolved from autocorrelation measurement with 9 ps time-tagger measurement jitter, 8 ps 1550 nm optical pulse. Estimated ± 2 ps error.

Further details on measurements are available upon request.

For system support, maintenance, or upgrades contact support@quantumopus.com.