

**ATTENTION:** POUR TOUTE INTERVENTION SUR L' APPLIQUE, COUPER L' ALIMENTATION.  
**CAREFUL:** FOR THIS OPERATION YOU HAVE TO CUT OFF THE POWER.  
**ACHTUNG:** FUR DIESE HAND HABUNG MUB DER STROM UNTERBROCHEN.  
**CUIDADO:** PARA CUALQUIER INTERVENCION EN EL APPLIQUE, CORTAR LA ALIMENTACION ELECTRICA.  
**ATTENZIONE:** PER QUELUNQUE INTERVENTO SULL' APPLIQUE INTERROMPERE L' ALIMENTAZIONE ELETTRICA.

|                                                      |                                                 |                                                    |                                                         |                                                      |
|------------------------------------------------------|-------------------------------------------------|----------------------------------------------------|---------------------------------------------------------|------------------------------------------------------|
| Luminaire Classe 2                                   | Classe 2 lamp                                   | Leuchten Klasse 2                                  | Luminario de clase 2                                    | Lume Classe 2                                        |
| Type de lampe:<br><b>Halogène GU10</b><br>50W / GU10 | Bulb type:<br><b>Halogen GU10</b><br>50W / GU10 | Glasbime typ:<br><b>Halogen GU10</b><br>50W / GU10 | Lipo de bombilla:<br><b>Halogena GU10</b><br>50W / GU10 | Typo di ampola:<br><b>Alogena GU10</b><br>50W / GU10 |

**MAXI : 50W / GU10**

Tension: 230 / 240 Volts.  
Fréquence: 50 Hertz.

**ATELIER SEDAP**  
LES BEAUX ARTS DU PLÂTRE

018020531-0

