

MRI IAC WO			
Technical Parameters			
Anatomic Coverage:	Midline of brainstem through the semicircular canals		
Coil:	Head		
Scanner Preference:			
Scanning Plane:	Axial	Axial	Axial
Slice Thickness:	0.5mm	0.5mm	2mm
Gap:	0mm	0mm	0.2mm
Weighting:	T2	T1	DWI
Mode:	3D TSE	3D TSE	2D TSE or RESOLVE
FAT SAT:	NO	NO	YES
FOV:	17cm	17cm	17cm
MPR:	COR, SAG, OBLIQ	COR, SAG	NO
Notes:			